










HAOYU



SCHEMATIC



P.C.B LAYOUT

SPECIFICATION

- 1.Rating : DC12V 50mA.
 - 2.Contact resistance: $\leq 100m\Omega$.
 - 3.Insulation resistance: $\geq 100M\Omega$ (DC250V).
 - 4.Withstanding voltage: 250VAC .
 - 5.Operating Force: 160 $\pm$ 50gf/250 $\pm$ 80gf (依客户需求而定) .
 - 6.Travel:0.3 $\pm$ 0.2mm.
 - 7.life test: 10,000 cycles.
 - 8.Operation temperature range:-40 $^{\circ}$ C~85 $^{\circ}$ C.
 - 9.Sign"* "is importance dimension.
- 防水等级: IP67

0769-82310511-867

高度H	按钮字母
12.85	S
13.0	H
15.0	T红色

					TOLERANCE UNLESS SPECIFIED									
7	TERMINAL	BRASS	2	Ag-PLATED	<1.5: ±0.1mm >1.5~5.0: ±0.25mm >5.0: ±0.3mm	ANGULAR ±1°								
6	HOUSING	PBT	1	BLACK										
5	SPRING	PHOSPHOR BRONZE	1	Ag-PLATED			NO	DATE	REVISIONS			BY	APPD	
4	WATERPROOF FILM	PI	1	YELLOW			TITLE: TACT SWITCH			UNIT : MM	ROHS	DWN		
3	WATERPROOF PAD	SILICA GEL	1	BLACK	MODEL: TC-00108FA-150E-03			SCALE: 1:1	COMPLIANT	CHK'D				
2	COVER	PBT	1	BLACK	 DONGGUANG HAOYU ELECTRONICS CO., LTD 皓宇 东莞市弘皓电子有限公司							APPD		
1	BUTTON	PBT	2	BLACK										
NO.	PART	NAME	MATERIAL	QTY	FINISHING								PRO.AGL: 	REV :A0