







0769-82310511-867

DC MATE PLUG

DC JACK

技术要求:

1. 电气参数: 48VDC 5A 5000Cycle;
2. 操作环境温度: -25° c~85° c;
3. 线材外观光滑, 平整, 绝缘护套不得有划伤残缺等不良现象;
4. 端子压接比: 65%~90%;
5. 耐压: 250Vac 1分钟;
6. 连接器拉脱力: 单根线>30N;
7. DC JACK插拔力: (3~30) N;
8. 环保要求: 符合Rohs/Reach;
9. 带" * "尺寸为品质重点管控尺寸;

				TOLERANCE UNLESS SPECIFIED							
				UP TO 5mm: ±0.1	ANGULAR						
				ABOVE 5mm: ±0.2	±1°	NO	DATE	REVISIONS		BY	APPD
6	Heat shrinkable tube	10mm Black	2pcs	TITLE: DC JACK ASSY				UNIT : MM	ROHS	DWN	
5	WIRE	UL3302#22 Black	1pc	MODEL:DC-086-2.1-PU-SH073				SCALE: 4:1	COMPLIANT	CHK'D	
4	WIRE	UL3302#22 Red	1pc	 HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司				APPD			
3	Connector Terminal	PH-AT11有字磷铜后镀镍底	2pcs								
2	Connector Base	PHR-2A(V0)	1pc								
1	DC JACK	DC-086 φ2.1-PU	1pc								
NO	PART NAME	PART DESCRIPTION	Qty.					PRO.AGL: 		REV :A0	