




SPECIFICATION

1. Rating : AC 100V 2A.
2. Contact resistance: $\leq 50\text{m}\Omega$.
3. Insulation resistance: $\geq 100\text{M}\Omega$ (DC250V).
4. Withstanding voltage: 500VAC .
5. Insertion and extraction force: 10-60N
5. life test: 5000 cycles.
6. Operation temperature range: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
7. Sign"* "is importance dimension.

0769-82310511-867

NO.	PART NAME	MATERIAL	QTY	FINISHING	TOLERANCE UNLESS SPECIFIED		DATE	REVISIONS	BY	APPD
					<1.5: $\pm 0.1\text{mm}$ >1.5~5.0: $\pm 0.25\text{mm}$ >5.0: $\pm 0.3\text{mm}$	ANGULAR $\pm 1^{\circ}$				
4	COVER	PBT	1		TITLE: DIN JACK		UNIT : MM	ROHS	DWN	
3	CONTACT FOOT	BRASS	5	CuSn-PLATED	MODEL: DIN-504B		SCALE: 1:1	COMPLIANT	CHK'D	
2	EARTH TERMINAL	PHOSPHOR BRONZE	1	CuSn-PLATED	 DONGGUANG HAOYU ELECTRONICS CO., LTD 皓宇 东莞市弘皓电子有限公司		APPD			
1	HOUSING	PBT	1				PRO.AGL: 		REV :A2	