






Engineer Drawing



■ SPECIFICATIONS :

- Voltage Rating: 250V AC / DC
- Current Rating: 3A AC / DC
- Withstanding Voltage: 1500V AC/minute
- Temperature Range: -25°C~+85°C
- Insulation Resistance: 1000MΩMin.
- Contact Resistance: 20mΩ Max.

■ *Material:

Terminal: Phosphor Bronze

Plating: Tin Plated Or Gold Flash

Or Contact Gold Flash Bottom Nickel

IPCW 254 T 07 X X X X X

Series Type

Pitch:3.0mm

Connector Type

Serial Code

Material Code

Other Code

Terminal

Other Code

Plating:T=Tin

GENERAL
TOLERANCES:

X.=±0.30

X.X=±0.20

X.XX=±0.10

NCP

www.i-ncp.com

PART NO:
IPCW254T07 xx ET

DRAWING NO
IPCW254T07ET

 SHEET 1 OF 1

NAME:
2.54mm Pitch Terminal Tight
Type AWG #22 ~ #26

UNITS:mm SCALE:1:1 REV.01