








PIN NO	SIGNAL NAME	PIN NO	SIGNAL NAME
A1	GND	B12	GND
A2	TXp1	B11	RXp1
A3	TXn1	B10	RXn1
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	Dp1	B7	Dn2
A7	Dn1	B6	Dp2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10	RXn2	B3	TXn2
A11	RXp2	B2	TXp2
A12	GND	B1	GND

0769-82310511-867

SPECIFICATION

1.Rating : 20V DC/AC

Vbus电流5A最大, GND电流5A最大, 其他PIN 0.25A最大.

2.Contact resistance: ≤50mΩ.

3.Insulation resistance: ≥100MΩ (DC100V).

4.Withstanding voltage: 100VAC .

5.INSERTION FORCE:5-20N/ REMOVAL FORCE: 8-20N

6.life test: 10000 cycles.

7.Operation temperature range:-25℃~85℃.

8.Sign"* "is importance dimension.

TID: 7736

				TOLERANCE UNLESS SPECIFIED							
				<1.5: ±0.1mm >1.5~5.0: ±0.25mm >5.0: ±0.3mm	ANGULAR ±1°	A0	2024.8.19	首次发行		YKH	
						NO	DATE	REVISIONS		BY	APPD
5	EMI PLATE	STEEL	1					UNIT : MM	ROHS	DWN	
4	FRONT SHELL	STEEL	1	Ni-PLATED				SCALE: 1:1	COMPLIANT	CHK'D	
3	MID PLATE	STEEL	1	SN-PLATED						APPD	
2	CONTACTS	CUETP	24	Au-PLATED							
1	HOUSING	PA9T(UL94V-0)	1	BLACK							
NO.	PART	NAME	MATERIAL	QTY	FINISHING						

DONGGUANG HAOYU ELECTRONICS CO., LTD
皓宇
东莞市弘皓电子有限公司

PRO.AGL: REV :A0