







SCHEMATIC



P.C.B LAYOUT



H=4.8mm

SPECIFICATION

- 1.Rating : DC12V 50mA.
- 2.Contact resistance: $\leq 100m\Omega$.
- 3.Insulation resistance: $\geq 100M\Omega$ (DC250V).
- 4.Withstanding voltage: 250VAC .
- 5.Operating Force: $160\pm 50gf$.
- 6.Travel: $0.2\pm 0.1mm$.
- 7.life test: 10,000 cycles.
- 8.Operation temperature range: $-25^{\circ}C\sim 85^{\circ}C$.
- 9.Sign"* "is importance dimension.

0769-82310511-867

					TOLERANCE UNLESS SPECIFIED								
					<1.5: ±0.1mm >1.5~5.0: ±0.25mm >5.0: ±0.3mm	ANGULAR ±1°							
5	TERMINAL	BRASS	2	Ag-Plated			NO	DATE	REVISIONS			BY	APPD
4	CASE	PA6T	1	BLACK	TITLE: TACT SWITCH				UNIT : MM	ROHS	DWN		
3	REED	SUS	1	Ag-Plated	MODEL: TC-00204V-048C-03				SCALE: 1:1	COMPLIANT	CHK'D		
2	FRAME	SPCC	1	Sn-Plated	 皓宇 HAOYU DONGGUANG HAOYU ELECTRONICS CO., LTD 东莞市弘皓电子有限公司						APPD		
1	KNOB	PA6T	1	BLACK									
NO.	PART NAME	MATERIAL	QTY	FINISHING							PRO.AGL:		REV :A0