


SPECIFICATIONS

- 1、Current Rating: 5A AC, DC
 - 2、Voltage Rating: 250V AC, DC
 - 3、Temperatuer Range: -40℃~ +105℃
 - 4、Contact Resistance: 20mΩ Max
 - 5、Insulation Resistance: 1000mΩ Min
 - 6、Withstanding Voltang: 1000V AC/minute
 - 7、Material: Phosphoric bronze Tin-plated
 - 8、Applicable Wire Sizes:AWG#20~28#
- Qty/Reel: 10000 PCS

			GENErl TOLerANCE	制 图 DRAWING	 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD				
			DIM TOL	审 核 CHECK					
			X. X ±0.30	批 准 APPROVAL	产品名称 TITLE	MX (3.00) 公端子	版 本 REV.	A	
1	初版发行		X. XX ±0.20	比 例 SCALE	产品料号 PART NO.	HC-MX3.0-PT-05	单 位 UNITS	mm	
			X. XXX ±0.10	投 影 Projection	材 料 MATERIAL		页 次 SHEET	1/1	
序号 No.	变更内容 MODIFY CONTENT	日 期 MODIFY DATE	Angle ±3.0°						