

1				2				3				4				5				6				7				8							
High photosynthesis (H)				The female seat height (H1)				The male seat height (H2)				Insertion height (H3)				REV				ECN				DESCRIPTION				MDF' D				DATE			
3.0				2.2				0.8				1.6				1.0				/				新发行								2021-07-08			
3.5				2.2				1.3				1.6																							
4.0				3.0				1.0				1.9																							
4.5				3.5				1.0				1.9																							
5.0				3.0/4.0				2.0/1.0				1.9																							
5.5				3.5/4.5				2.0/1.0				1.9																							
6.0				4.0				2.0				1.9																							
6.5				4.5				2.0				1.9																							
7.0				3.0				4.0				1.9																							
7.5				3.5				4.0				1.9																							
8.0				4.0				4.0				1.9																							
8.5				4.5				4.0				1.9																							

ASSEMBLY

NO. of Contacts	Dimension (mm)				
	A±0.10	B±0.10	C±0.10	D±0.10	E±0.10
6	4.20	1.00	2.90	2.06	
8	4.70	1.50	3.40	2.56	
10	5.20	2.00	3.90	3.06	
12	5.70	2.50	4.40	3.56	
14	6.20	3.00	4.90	4.06	
16	6.70	3.50	5.40	4.56	
18	7.20	4.00	5.90	5.06	
20	7.70	4.50	6.40	5.56	
22	8.20	5.00	6.90	6.06	
24	8.70	5.50	7.40	6.56	
26	9.20	6.00	7.90	7.06	
28	9.70	6.50	8.40	7.56	
30	10.20	7.00	8.90	8.06	
32	10.70	7.50	9.40	8.56	
34	11.20	8.00	9.90	9.06	
36	11.70	8.50	10.40	9.56	
38	12.20	9.00	10.90	10.06	
40	12.70	9.50	11.40	10.56	
42	13.20	10.00	11.90	11.06	
44	13.70	10.50	12.40	11.56	
46	14.20	11.00	12.90	12.06	
48	14.70	11.50	13.40	12.56	
50	15.20	12.00	13.90	13.06	
52	15.70	12.50	14.40	13.56	
54	16.20	13.00	14.90	14.06	
56	16.70	13.50	15.40	14.56	
58	17.20	14.00	15.90	15.06	
60	17.70	14.50	16.40	15.56	
62	18.20	15.00	16.90	16.06	
64	18.70	15.50	17.40	16.56	
66	19.20	16.00	17.90	17.06	
68	19.70	16.50	18.40	17.56	
70	20.20	17.00	18.90	18.06	
72	20.70	17.50	19.40	18.56	
74	21.20	18.00	19.90	19.06	
76	21.70	18.50	20.40	19.56	
78	22.20	19.00	20.90	20.06	
80	22.70	19.50	21.40	20.56	
82	23.20	20.00	21.90	21.06	
84	23.70	20.50	22.40	21.56	
86	24.20	21.00	22.90	22.06	
88	24.70	21.50	23.40	22.56	
90	25.20	22.00	23.90	23.06	
92	25.70	22.50	24.40	23.56	
94	26.20	23.00	24.90	24.06	
96	26.70	23.50	25.40	24.56	
98	27.20	24.00	25.90	25.06	
100	27.70	24.50	26.40	25.56	

P.B.C LAYOUT

5.60
1.50
4.00±0.10
5.20±0.10

HX-BTB F 0522-2×NP

PIN

HEIGHT: 22-2.2H; 30-3.0H
35-3.5H; 40-4.0H
45-4.5H.

0.5BTB

FEMALE

JM CONN BTB CONNECTOR SERIES

.X ±0.20		.X° ±1.0°				深圳市韩下电子有限公司	
.XX ±0.10		.XX° ±0.5°					
.XXX ±0.05		.XXX° ±0.2°		Part Name: HX-BTB F0522-2x30P		Approved: 罗小春	
		SCALE 1:1		UNIT mm		Part No.:	
PAGE: 1/1		REV: 1.0		Title:		Material:---	
				Drawing No.:		Mode NO.:	
						Date: 2021-07-08	

No.	品名	数量	材料	表面处理	备注
1	端子	PIN数	C5191 H	全金Flash 0.6U"	
2	本体	1	PANT 黑色		
3	CAP	1	PANT 黑色		