








公差参数

Poles	Dim	Dim P	Dim L
2-6P		±0.10	±0.15
7-12P		±0.20	±0.20
13-18P		±0.25	±0.30
19-24P		±0.30	±0.40



材料及电镀

- ①. 塑件主体: PA66, UL94V-0
②. 焊 针: 黄铜, 镀镍

电气性能

额定电压: 300V
额定电流: 8A
接触电阻: 20mΩ (Max)
绝缘电阻: 500MΩ \DC1000V
耐 电 压: AC1500V\1Min

机械性能

温度范围: -40℃ ~ +105℃
瞬时温度: +250℃ ,5秒

Ordering Information

HC15EDG * * - * - NP - *

Type	Pitch	No. of Pins	Colour
V=Green B=Blue R=Red	2.54=2.54mm 3.5=3.50mm 3.81=3.81mm 5.08=5.08mm 7.62=7.62mm	2-24Pin 2P=2Pin 3P=3Pin	V=Green B=Blue O=Orange R=Red B=Black GR=Gray

GENERAL TOLERANCE			制 图	深圳市华灿天禄电子有限公司			
DIM TOL			DRAWING	ShenzhenhuacantianluELECTRONICS CO., LTD			
X.X ±0.50			审 核	产品名称	3.81 单排 插拔式 接线端子	版本	A
X.XX ±0.30			批 准	TITLE	封闭 弯针	REV.	
X.XXX ±0.10			比 例	产品料号	HC15EDGRC-3.81-NP-X	单 位	mm
Angle ±3.0°			投 影	PART NO.		页 次	1/1
序号	变更内容	日期	Projection	MATERIAL		SHEET	
No.	MODIFY CONTENT	MODIFY DATE					