

D

C

B

A

D


C

B

A

Kinghelm®

| REVISIONS |        |             |       |     |      |
|-----------|--------|-------------|-------|-----|------|
| REV       | NUMBER | DESCRIPTION | DWN   | CHK | DATE |
| A         |        | DESIGN      | James |     | 9/26 |
|           |        |             |       |     |      |



NOTES:

- ELECTRICAL:
  - VOLTAGE RATING:DCV 300V 10MS
  - CONDUCTANCE RESISTANCE: 3.0 OHM/MAX.
  - INSULATION RESISTANCE: 5.0M OHM/MIN.
  - THE CABLE SHOULD BE 100% ELECTRICAL TEST
  - IT SHOULD BE NO ANY OPEN/SHORT, MISWIRING AND INTERMITTENT FAILURES.
- MATERIAL:
  - SEE TABLE
- ALL COMPONENTS ARE RoHS COMPLIANT.

| ITEM NO. | PART NUMBER | DESCRIPTION          | QTY. |
|----------|-------------|----------------------|------|
| ④        | 套管          | OD:2.5* 15 mm 套管     | 2    |
| ③        | 接头          | SMB母头母针, 直头, 镀金      |      |
| ②        | 接头          | SMB母头母针, 直头, 镀金      | 2    |
| ①        | 同轴线         | RG1.37黑色线, OD:1.37mm | AS   |

深圳市金航标电子有限公司  
SHENZHEN KINGHELM ELECTRON CO., LTD.

|                                                                     |                                                                         |                    |                                        |
|---------------------------------------------------------------------|-------------------------------------------------------------------------|--------------------|----------------------------------------|
| ALL DIMENSION<br>ARE IN MM                                          | DRAWN<br>James                                                          | DATE<br>2025-03-10 | TITLE<br><br>KH-SMBK-SMBK-RG1.37-140MM |
|                                                                     | CHKD.<br>Frank                                                          | 2025-03-10         |                                        |
|                                                                     | APPD.<br>Scott                                                          | 2025-03-10         |                                        |
| COMPUTER GENERATED<br>IN SOLIDWORKS<br>DO NOT SCALE<br>THIS DRAWING |                                                                         |                    | SIZE DWG Number.                       |
| PROJECTION<br>                                                      | GENERAL TOLERANCE FOR<br>ANGLES X.X X.XX X.XXX<br>±1° ±0.3 ±0.25 ±0.150 |                    | REV<br>A                               |
| SCALE:Free                                                          |                                                                         | TYPE               | SHEET 1 OF 1                           |

CUSTOMER P/N: