




Kinghelm®


| REVISIONS |        |             |       |     |      |
|-----------|--------|-------------|-------|-----|------|
| REV       | NUMBER | DESCRIPTION | DWN   | CHK | DATE |
| A         |        | DESIGN      | James |     | 9/26 |
|           |        |             |       |     |      |

NOTES:

1. ELECTRICAL:
- 1.1. VOLTAGE RATING:DCV 300V 10MS
- 1.2. CONDUCTANCE RESISTANCE: 3.0 OHM/MAX.
- 1.3. INSULATION RESISTANCE: 5.0M OHM/MIN.
- 1.4. THE CABLE SHOULD BE 100% ELECTRICAL TEST
- 1.5. IT SHOULD BE NO ANY OPEN/SHORT, MISWIRING AND INTERMITTENT FAILURES.
2. MATERIAL:
- 2.1. SEE TABLE
3. ALL COMPONENTS ARE RoHS COMPLIANT.

| ITEM NO. | PART NUMBER | DESCRIPTION        | QTY. |
|----------|-------------|--------------------|------|
| ④        | 套管          | OD:3.5* 15 mm 套管   | 2    |
| ③        | 接头          | SMB公头公针, 直头, 镀金    |      |
| ②        | 接头          | SMB公头公针, 直头, 镀金    | 2    |
| ①        | 同轴线         | RG316棕色线, OD:2.5mm | AS   |

深圳市金航标电子有限公司  
SHENZHEN KINGHELM ELECTRON CO., LTD.

|                                                                                       |                                                                         |       |      |            |  |  |                                       |             |         |      |
|---------------------------------------------------------------------------------------|-------------------------------------------------------------------------|-------|------|------------|--|--|---------------------------------------|-------------|---------|------|
| ALL DIMENSION<br>ARE IN MM                                                            | DRAWN                                                                   | James | DATE | 2025-03-10 |  |  | TITLE<br><br>KH-SMBJ-SMBJ-RG316-280MM |             |         |      |
|                                                                                       | CHKD.                                                                   | Frank |      | 2025-03-10 |  |  |                                       |             |         |      |
|                                                                                       | APPD.                                                                   | Scott |      | 2025-03-10 |  |  |                                       |             |         |      |
| COMPUTER GENERATED<br>IN SOLIDWORKS                                                   |                                                                         |       |      |            |  |  |                                       |             |         |      |
| DO NOT SCALE<br>THIS DRAWING                                                          |                                                                         |       |      |            |  |  |                                       |             |         |      |
| PROJECTION                                                                            | GENERAL TOLERANCE FOR<br>ANGLES X.X X.XX X.XXX<br>±1° ±0.3 ±0.25 ±0.150 |       |      |            |  |  | SIZE                                  | DWG Number. |         | REV  |
|  |                                                                         |       |      |            |  |  | B                                     |             |         | A    |
|                                                                                       |                                                                         |       |      |            |  |  | SCALE: Free                           | TYPE        | SHEET 1 | OF 1 |

CUSTOMER P/N: