




Kinghelm®

| REVISIONS |        |             |       |     |      |
|-----------|--------|-------------|-------|-----|------|
| REV       | NUMBER | DESCRIPTION | DWN   | CHK | DATE |
| A         |        | DESIGN      | James |     | 9/26 |
|           |        |             |       |     |      |

260±10

NOTES:

1. ELECTRICAL:
- 1.1. VOLTAGE RATING:DCV 300V 10MS
- 1.2. CONDUCTANCE RESISTANCE: 3.0 OHM/MAX.
- 1.3. INSULATION RESISTANCE: 5.0M OHM/MIN.
- 1.4. THE CABLE SHOULD BE 100% ELECTRICAL TEST
- 1.5. IT SHOULD BE NO ANY OPEN/SHORT, MISWIRING AND INTERMITTENT FAILURES.
2. MATERIAL:
- 2.1. SEE TABLE
3. ALL COMPONENTS ARE RoHS COMPLIANT.

| ITEM NO. | PART NUMBER | DESCRIPTION          | QTY. |
|----------|-------------|----------------------|------|
| ④        | 套管          | OD:3.5* 15 mm 套管     | 2    |
| ③        | 接头          | SMB公头公针, 直头, 镀金      |      |
| ②        | 接头          | SMB母头母针, 直头, 镀金      | 2    |
| ①        | 同轴线         | RG1.37黑色线, OD:1.37mm | AS   |

深圳市金航标电子有限公司  
SHENZHEN KINGHELM ELECTRON CO., LTD.

|                                                               |                                                                      |                 |                                    |
|---------------------------------------------------------------|----------------------------------------------------------------------|-----------------|------------------------------------|
| ALL DIMENSION ARE IN MM                                       | DRAWN James                                                          | DATE 2025-03-10 | TITLE<br>KH-SMBJ-SMBK-RG1.37-260MM |
|                                                               | CHKD. Frank                                                          | 2025-03-10      |                                    |
| COMPUTER GENERATED IN SOLIDWORKS<br>DO NOT SCALE THIS DRAWING | APPD. Scott                                                          | 2025-03-10      |                                    |
|                                                               |                                                                      |                 | SIZE DWG Number.                   |
| PROJECTION                                                    | GENERAL TOLERANCE FOR ANGLES X.X X.XX X.XXX<br>±1° ±0.3 ±0.25 ±0.150 |                 | REV A                              |
| SCALE:Free                                                    |                                                                      | TYPE            | SHEET 1 OF 1                       |

CUSTOMER P/N: