

2510

4,8

220

13

5, 8

Technical drawing of the cable connector assembly. The drawing shows two views of the connector. The top view is a side profile showing the cable (1) entering the connector body (3). The bottom view is a front view showing the cable (1) with a positive (+) and negative (-) polarity marking. Dimensions are indicated in yellow text: 7,97 for the length of the connector body and 0,4 for the width of the cable. Callouts 1, 3, 4, and 5 point to the cable, connector body, cable jacket, and cable braid respectively.

② 20AWG

TOLERANCE:
X.X $\pm 0.2\text{mm}$
X.XX $\pm 0.05\text{mm}$
X.XXX $\pm 0.005\text{mm}$

must-see 必看:

日期: 25 3 1

批准:


名称: cx-906-8mm母

材质： 重量：

DRAWN:周海波 CHECKED:周丕霞 APPROVED:

SCALE
1:1

THIRD ANGLE



1	塑料			PVC	黑	20AWG
2	线			PVC	蓝	
3	针			3U	镀金	
4	磁铁			N52	镀镍	
5	铜壳			H59	镀镍	
6						
序号	零件代号	名 称	数 量	材 料	镀层, 颜色	备 注