





Rev.	ECN	Number	Description	Date	Drawn	Checkd	Approved




焊盘尺寸
尺寸公差 ±0.05



技术要求:

- 1.材质:不锈钢SUS301,T=0.15±0.005;
- 2.端子锡脚焊接面和接触面不可有毛边,其他部位毛边最大0.03mm;
- 3.扭曲:45°/1000mm,拱形 5mm/1000mm;
- 4.标示有“▼”符号的为重点控制和检验尺寸;
- 5.未标注之R MAX R0.13;
- 6.电镀须满足24小时盐雾测试;
- 7.寿命测试>2万次,产品弹力要求在60gf~80gf之间
- 8.镍底50~80u"min,产品外表面镀锡80~100U"MIN



YDC
深圳市玥达电子科技有限公司
Shenzhen Yueda Electronic Technology Co.,Ltd.

GENERAL TOLERANCE		
XX. ±0.50		
X. ±0.35	X' ±2.0'	
.X ±0.25	.X' ±1.0'	
.XX ±0.15	.XX' ±0.5'	

SCALE:	1:1
UNIT:	mm
SIZE:	A4

DRAWN	DATE
CHECK	DATE
APPROVE	DATE

DWG. NO.	
PARTS NO.(INTENDED USE)	
YDC-LCZJA1-076	

TITLE	客户图
SHIELD CAN CLIP	
L5.20*W1.2*H1.30mm(夹0.2料厚)	

REV.	A
SHEET	1/1