



Rev.	ECN	Number	Description	Date	Drawn	Checkd	Approved

Ø0.90 PICK UP AREA



1.05±0.05



0.20±0.15

0.10 A

-A-


2.00
2.30
3.50±0.10
0.08

0.90±0.15

T=0.10


1.50
2.00
2.53±0.08

正常自由高度



0.60


1.50±0.08



Ø0.60

1.00

1.15



2.10


1.50

焊盘尺寸

尺寸公差 ±0.05

技术要求:

- 1.材质:不锈钢SUS301,T=0.10±0.005;
- 2.端子锡脚焊接面和接触面不可有毛边,其他部位毛边最大0.03mm;
- 3.扭曲:45°/1000mm,拱形 5mm/1000mm;
- 4.标示有“▼”符号的为重点控制和检验尺寸;
- 5.未标注之R MAX R0.13;
- 6.电镀须满足24 小时盐雾测试;
- 7.寿命测试>2万次,产品弹力要求在60gf~80gf之间
- 8.镍底50~80u"min,焊接区域镀金,接触区域镀金1U"MIN



深圳市玥达电子科技有限公司
Shenzhen Yueda Electronic Technology Co.,Ltd.

GENERAL TOLERANCE

XX. ±0.50	X. ±0.35	X' ±2.0'
.X ±0.25	.X' ±1.0'	
.XX ±0.15	.XX' ±0.5'	

SCALE:


1:1

UNIT:

mm

SIZE:

A4



DRAWN

CHECK

APPROVE

DATE

DATE

DATE

DWG. NO.

PARTS NO.(INTENDED USE)

YDC-LCTP-A1-021

TITLE

客户图

RF Antenna Spring,SMT,
L3.5*W1.5*H2.5mm

REV.

A

SHEET

1/1