







Rev.	ECN	Number	Description	Date	Drawn	Checkd	Approved

技术要求:

- 1.材质:不锈钢SUS301, $T=0.15\pm0.005$;
- 2.端子锡脚焊接面和接触面不可有毛边,其他部位毛边最大0.03mm;
- 3.扭曲: $45^{\circ}/1000\text{mm}$,拱形 $5\text{mm}/1000\text{mm}$;
- 4.标示有“▼”符号的为重点控制和检验尺寸;
- 5.未标注之R MAX R0.13;
- 6.电镀须满足24小时盐雾测试;
- 7.寿命测试>2万次,产品弹力要求在60gf~80gf之间
- 8.镍底50 80u"min,产品外表面镀锡80~100U"MIN



焊盘尺寸
尺寸公差 ± 0.05

YDC
深圳市玥达电子科技有限公司
Shenzhen Yueda Electronic Technology Co., Ltd.

GENERAL TOLERANCE		
XX. ± 0.50	X: $\pm 2.0^{\circ}$.X: $\pm 1.0^{\circ}$.XX: $\pm 0.5^{\circ}$	
X. ± 0.35		
.X ± 0.25		
.XX ± 0.15		

SCALE: 1:1
UNIT: mm
SIZE: A4

DRAWN
CHECK
APPROVE

DATE
DATE
DATE
DWG. NO.
PARTS NO.(INTENDED USE)
YDC-LCZJ-A1-070

TITLE
客户图
SHIELD CAN CLIP
L6.50*W0.8*H1.28mm(夹0.15料厚)

REV. A
SHEET 1/1