



CUSTOMER(客户):			PAGE: 1 OF 2																																
ITEM: LCD32-22UH			Customer's ITEM:																																
Item 项目	Spec.(mm) 规格值	Typ. 实测值	1. MECHANICAL DIMENSIONS(外形尺寸): 																																
A	3.0± 0.3	3.23																																	
B	3.5± 0.3	3.52																																	
C	2.0± 0.3	2.12																																	
D																																			
E																																			
F																																			
G																																			
H																																			
I																																			
J																																			
Marking(印字): 220																																			
2.ELECTRICAL CHARACTERISTICS(电特性要求): <table><tr><th>ITEM (项目)</th><th>Specifications(规格值)</th><th>Typ.(参考值)</th><th>Test equipments(测试仪器)</th></tr><tr><td>L</td><td>22UH ± 20%</td><td></td><td>TH2817B LCR METER.</td></tr><tr><td>Test Freq.</td><td>@100kHz 0.25V</td><td></td><td>TH2817B LCR METER.</td></tr><tr><td>DCR</td><td>708MΩ</td><td></td><td>VR 131 LCR METER.</td></tr><tr><td>R.Current</td><td>0.50A</td><td></td><td>VR126</td></tr><tr><td>Ope.Temp.</td><td>-20℃ TO 80℃</td><td></td><td>HC-D3M TEMP. & HUMIDITY CHAMBER</td></tr><tr><td>Others</td><td></td><td></td><td></td></tr><tr><td></td><td></td><td></td><td></td></tr></table>				ITEM (项目)	Specifications(规格值)	Typ.(参考值)	Test equipments(测试仪器)	L	22UH ± 20%		TH2817B LCR METER.	Test Freq.	@100kHz 0.25V		TH2817B LCR METER.	DCR	708MΩ		VR 131 LCR METER.	R.Current	0.50A		VR126	Ope.Temp.	-20℃ TO 80℃		HC-D3M TEMP. & HUMIDITY CHAMBER	Others							
ITEM (项目)	Specifications(规格值)	Typ.(参考值)	Test equipments(测试仪器)																																
L	22UH ± 20%		TH2817B LCR METER.																																
Test Freq.	@100kHz 0.25V		TH2817B LCR METER.																																
DCR	708MΩ		VR 131 LCR METER.																																
R.Current	0.50A		VR126																																
Ope.Temp.	-20℃ TO 80℃		HC-D3M TEMP. & HUMIDITY CHAMBER																																
Others																																			


CUSTOMER(客户):	PAGE: 2 OF 2
ITEM: LCD32-22UH	Customer's ITEM:

◆、卷盘尺寸 (单位:mm)



A	2.3±0.2
B	10.75±0.2
C1	330±1
D	φ100±0.2
H	12.5±0.2
T	2.3±0.2
颜色	蓝色

◆、载带尺寸 (单位:mm)



项目	W	P	P0	T
规格	12.00	8.00	4.00	0.40
公差	±0.3	±0.1	±0.1	±0.05