


Tolerance:  $\pm 0.05\text{mm}$

NOTE:

1. MECHANICAL PERFORMANCE,  
1.1 INSERTION FORCE: 0.5-2.0N

- 1-2. INSERTION FORCE: 0.5~2.0kgf.

A1	GND	B12	GND
A2	SSTXP1	B11	SSTXP1



NO	DESCRIPTION	QTY	MATERIAL	REMARKS
----	-------------	-----	----------	---------

UNLESS OTHERWISE  
SPECIFIED, TOLERANCES



东莞市汉博电子科技有限公司

DECIMALS:      ANGLES:

TYPE C 24PIN卧式半插半贴 1PX7	
-------------------------	--

CUSTOMER COPY	