



REV.	ECN NO OR DESCRIPTION	REVISED	DATE

SPECIFICATION NOTES:

ELECTRICAL:






1. VOLTAGE RATING: 125 VAC RMS
2. CURRENT RATING: 1.5 AMP
3. CONTACT RESISTANCE: 30mΩ MAX.
4. INSULATION RESISTANCE: 500MΩMIN. AT 500V DC.
5. DIELECTRIC STRENGTH: 1000 VAC 50Hz 1MINUTE

MECHANICAL:



1. HOUSING MATERIAL:
SEE PART NUMBER.
2. CONTACTS: Ø0.46mm PHOSPHOR BRONZE, GOLD
PLATING OVER NICKEL
3. SHIELD: 0.20mm THICKNESS COPPER ALLOY WITH
NICKEL PLATED.
4. OPERATING LIFE: 750 CYCLES MIN.
5. MATING FORCE: 22N MAX.
UNMATING FORCE: 22N MAX.
6. Wave soldering Temp.: 235°±5°

ENVIRONMENTAL:

1. STORAGE: -40°C TO +85°C
2. OPERATION: -40°C TO +85°C



Recommend PCB Layout
TOLERANCES: ±0.05



UNLESS OTHERWISE SPECIFIED TOLERANCES		 东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD			
DECIMALS: ANGLES:		TITLE RJ45 5224 8P8C 全包带灯 左黄右绿脚厚3.85			
X :±0.35 X :±2°	DWN xiong PART NO. RJ45-5211881B15-B				
X.X :±0.25 X.X :±1°	CHKD lee SCALE:1:1 UNIT: mm 				
X.XX :±0.15	APVD wang SIZE: A4 SHEET:10F 1 REV: A4				
CUSTOMER COPY					