



REV.	ECN NO OR DESCRIPTION	REVISED	DATE

NOTES









- MATERIAL
1. HOUSING MATERIAL:THERMO PLASTICS UL94V-0 COLOR BLACK.
2. CONTACT MATERIAL :PHOSPHOR BRONZE T=0.25mm.
: SELECT GOLD PLATING ON CONTACT AREA AND TIN
PLATING ON SOLDER AREA OVER NICKEL.
3. SHIELD: STAINLESS T=0.20mm NI PLATING.
4. GASKET :SPCC T=0.40 NI PLATING.

- MELECTRICAL
1. VOLTAGE RATING:125 VAC RMS.
2. CURRENT RATING:1.5 AMP.
3. CONTACT RESISTANCE:40 MILLIOHMS MAX.
4. INSULATION RESISTANCE:500 MEGOHMS MIN @ 100V DC .
5. DIELECTRIC DIELECTRIC
RESISTANCE:500V DC RMS 50Hz. 1MIN.

- MECHANICAL
1. DURRABILITY:750 CYCLES MIN.
2. MATING/UNMATING FORCE : 2.24 KG.F MAX.

- ENVIRONMENTAL:
1. STORAGE: -40℃~+85℃.
2. OPERATION: -40℃~+85℃.

8	—
7	—
6	RX-
5	—
4	—
3	RX+
2	TX-
1	TX+
PIN序说明	



PCBLAYOUT T=1.2
TOL:±0.05

RJ45-3005-201-21

流水码
11:GF LCP黑 盘装
21:GF LCP黑 卷装

类别码
201: 9.9H沉板5.8有壳无灯

UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS: ANGLES:

X :±0.30 X :±2°

X.X :±0.20 X.X :±1°

X.XX :±0.10



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

TITLE	RJ45 沉板5.8 DIP有壳无灯GF LCP黑			
DWN	xiong	PART NO. RJ45-3005-201-21		
CHKD	lee	SCALE:1:1	UNIT: mm	
APVD	wang	SIZE: A4	SHEET:10F 1	REV: A4

CUSTOMER COPY