










PCB LAYOUT



LED LAYOUT

LED Specification

Standard LED Color	LED Wavelength	Foward(A)	Foward(V)
Yellow	568nm	20mA	1.85-2.45V
Green	585nm	20mA	1.7-2.2V



MATERIAL:
HOUSING:PA46,PBT,BLACK.
TERMINAL: PHOSPHOR BRONZE Ø0.46MM
G/FU"GOLD PLATING

SHIELD:C2680,T=0.20MM, 20 MIN NICKEL 'PLATING
NO ALL AREA

MACHANICAL:
DURABILITY: 750 CYCLES MIN,12.5MM/MINUTE.
INSERTION FORCE: 2.2KG.F MAX.
RETENTION STRENGTH : 7.7KG.F BETWEEN JACK AND PLUG.
OPERATING TEMPERATURE: -40℃~+85℃.
STORAGE TEMPERATURE: -40℃~+85℃.
ALL CRITICAL DIMENSIONS WITH "※"

VOLTAGE: 125 VOLTS AC.
CURRENT RATING : 1.5AMP.
DIELECTRIC STRENGTH: 1000 VAC RMS 50HZ OR 60HZ,1MIN.
INSULATION RESISTANCE: 500 MEGA OHMS MIN. INITIAL
AFTER 500V DC FOR 1 MINUTE.
CONTACT RESISTANCE: SINGLE TERMINAL 30 MILLIOHMS MAX.
INITIAL 50 MILLIOHMS MAX. AFTER
DURABILITY TEST.

			GENERL TOLERANCE		制图	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	审核				
			X.X	±0.30	批准	产品名称	网络插座 (2x1 带灯无弹)	版本	A
			X.XX	±0.20	APPROVAL	产品料号	HC-RJ45-059D-2x1-2-04	单位	mm
			X.XXX	±0.10	SCALE	PART NO.		页次	1/1
序号	变更内容	日期	Angle ±3.0°		投影	材料			
No.	MODIFY CONTENT	MODIFY DATE			Projection	MATERIAL			