



PCB LAYOUT



HB-EH $\frac{2}{1}$ - $\frac{254}{3}$ $\frac{XXX}{4}$ $\frac{X}{5}$ $\frac{X}{6}$ $\frac{XX}{7}$ $\frac{X}{8}$ - $\frac{XXX}{9}$

SPECIFIACATIONS

Current rating:3A AC, DC
Temperature range:-40℃~+105℃
Insulation resistance:1000MΩ Min.
Withstanding voltage:1000V AC/minute.
Contact resistance:20mΩ Max.

Material:
Insulator:PA6T UL94V-0
Contact:Brass
Plating:Gold flash plated

1:Series No:
FH-Pin Header
2:Welding Board Type:
2-180度直插/DIP
TYPE
3:Pitch:
100-1.00mm
127-1.27mm
200-2.00mm
254-2.54mm
4:PIN位/PIN bit:
2*1P=21P

5:颜色/Color:
B-Black
6:材料/Material:
1-PBT 2-PA6T
7:触点电镀/Contact Plating:
G0-Gold Flash
8:包装方式/Package Type:
P-袋装/PE B-盒装/BOX
T-管装/Tubing W-卷装/winding
9:其他备注/Other remarks

CSG PART NO.	Pins	A	B	C	D
HB-EH2-25425PB2GOB	2*5P	10.16	21.68	31.90	18.30
HB-EH2-25426PB2GOB	2*6P	12.70	24.22	34.44	20.84
HB-EH2-25427PB2GOB	2*7P	15.24	26.76	36.98	23.38
HB-EH2-25428PB2GOB	2*8P	17.78	29.30	39.52	25.92
HB-EH2-25429PB2GOB	2*9P	20.32	31.84	42.06	28.46
HB-EH2-254210PB2GOB	2*10P	22.86	34.38	44.60	31.00
HB-EH2-254211PB2GOB	2*11P	25.40	36.92	47.14	33.54
HB-EH2-254212PB2GOB	2*12P	27.94	39.46	49.68	36.08
HB-EH2-254213PB2GOB	2*13P	30.48	42.00	52.22	38.62
HB-EH2-254214PB2GOB	2*14P	33.02	44.54	54.76	41.16
HB-EH2-254215PB2GOB	2*15P	35.56	47.08	57.30	43.70
HB-EH2-254216PB2GOB	2*16P	38.10	49.62	59.84	46.24
HB-EH2-254217PB2GOB	2*17P	40.64	52.16	62.38	48.78
HB-EH2-254218PB2GOB	2*18P	43.18	54.70	64.92	51.32
HB-EH2-254219PB2GOB	2*19P	45.72	57.24	67.46	53.86
HB-EH2-254220PB2GOB	2*20P	48.26	59.78	70.00	56.40
HB-EH2-254221PB2GOB	2*21P	50.80	62.32	72.54	58.94
HB-EH2-254222PB2GOB	2*22P	53.34	64.86	75.08	61.48
HB-EH2-254223PB2GOB	2*23P	55.88	67.40	77.62	64.02
HB-EH2-254224PB2GOB	2*24P	58.42	69.94	80.16	66.56
HB-EH2-254225PB2GOB	2*25P	60.96	72.48	82.70	69.10
HB-EH2-254226PB2GOB	2*26P	63.50	75.02	85.24	71.64
HB-EH2-254227PB2GOB	2*27P	66.04	77.56	87.78	74.18
HB-EH2-254228PB2GOB	2*28P	68.58	80.10	90.32	76.72
HB-EH2-254229PB2GOB	2*29P	71.12	82.64	92.86	79.26
HB-EH2-254230PB2GOB	2*30P	73.66	85.18	95.40	81.80
HB-EH2-254231PB2GOB	2*31P	76.20	87.72	97.94	84.34
HB-EH2-254232PB2GOB	2*32P	78.74	90.26	100.48	86.88

UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS: ANGLES:
X :±0.30 X :±2°
X.X :±0.25 X.X :±1°
X.XX :±0.20



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

TITLE	2.54mm Ejector Header 2xPin Dual Row Straight DIP type			
DWN	xiong	PART NO. HB-EH2-254XXXXB2GOB		
CHKD	lee	SCALE:1:1	UNIT: mm	
APVD	wang	SIZE: A4	SHEET:10F 1	REV: A4
CUSTOMER COPY				