







焊脚尺寸以顺畅过孔规为准



PCBLAYOUT T=1.6mm  
TOL:±0.05

|         |     |
|---------|-----|
| 8       | —   |
| 7       | —   |
| 6       | RX- |
| 5       | —   |
| 4       | —   |
| 3       | RX+ |
| 2       | TX- |
| 1       | TX+ |
| PIN序 说明 |     |

#### NOTES

##### MATERIAL

1. HOUSING MATERIAL: GLASS FILLED POLYESTER UL94V-0.
2. CONTACT MATERIAL: PHOSPHOR BRONZE  $\phi 0.46\text{mm}$ .
3. PLATING: SELECT GOLD PLATING OVER NICKEL 50u".
4. SHIELD: BRASS TO. 20mm 40u" NICKEL PLATED.

##### ELECTRICAL

1. VOLTAGE RATING: 125 VAC RMS.
2. CURRENT RATING: 1.5 AMP.
3. CONTACT RESISTANCE: 40 MILLIOHMS MAX.
4. INSULATION RESISTANCE: 500 MEGOHMS MIN @ 100V DC.
5. DIELECTRIC RESISTANCE: 500V DC RMS 50Hz. 1MIN.

##### MECHANICAL

1. DURABILITY: 750 CYCLES MIN.
2. MATING/UNMATING FORC: 2.24 KG. F MAX.

##### ENVIRONMENTAL:

1. STORAGE: -40°C ~ +85°C.
2. OPERATION: -40°C ~ +85°C.

RJ45-202-05-23

流水码

21: 2.8脚-0.5u" 淡 PBT黑 盘装

23: 2.8脚-0.5u" 淡 PA46黑 盘装

类别码

05: B型无弹无灯

UNLESS OTHERWISE  
SPECIFIED TOLERANCES

DECIMALS: ANGLES:  
X : ±0.35 X : ±2°  
X.X : ±0.25 X.X : ±1°  
X.XX : ±0.15



东莞市汉博电子科技有限公司  
DONGGUAN HANBO TECHNOLOGY CO., LTD

|       |                          |                         |              |         |
|-------|--------------------------|-------------------------|--------------|---------|
| TITLE | RJ45 56B型无弹 无灯 DIP PA46黑 |                         |              |         |
| DWN   | xiong                    | PART NO. RJ45-202-05-23 |              |         |
| CHKD  | lee                      | SCALE: 1:1              | UNIT: mm     |         |
| APVD  | wang                     | SIZE: A4                | SHEET: 10F 1 | REV: A4 |

CUSTOMER COPY