



REV.	ECN NO OR DESCRIPTION	REVISED	DATE

NOTES

MATERIAL

1. HOUSING MATERIAL: GLASS FILLED POLYESTER UL94V-0.
2. CONTACT MATERIAL: PHOSPHOR BRONZE $\phi 0.46\text{mm}$.
3. PLATING: GOLD PLATING OVER NICKEL.

ELECTRICAL







1. VOLTAGE RATING: 125 VAC RMS.
2. CURRENT RATING: 1.5 AMP.
3. CONTACT RESISTANCE: 40 MILLIOHMS MAX.
4. INSULATION RESISTANCE: 500 MEGOHMS MIN @ 100V DC.
5. DIELECTRIC RESISTANCE: 500V DC RMS 50Hz. 1MIN.

MECHANICAL

1. DURABILITY: 750 CYCLES MIN.
2. MATING/UNMATING FORCE: 2.24 KG.F MAX.

ENVIRONMENTAL:

1. STORAGE: $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$.
2. OPERATION: $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$.



PCB LAYOUT

RJ 3306-005- 18

产品类别 以太网连接器

产品流水系列码

18:全塑2.8脚-0.5u"淡 PBT黑盘装

5621 1*1全塑

UNLESS OTHERWISE SPECIFIED TOLERANCES		东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD			
DECIMALS:	ANGLES:	TITLE	5621 1x1全塑DIP 2.8脚-0.5U"淡PBT黑		
X :±0.30	X :±2°	DWN	xiong	PART NO. RJ3306-005-18	
X.X :±0.20	X.X :±1°	CHKD	lee	SCALE:1:1	UNIT: mm
X.XX :±0.10		APVD	wang	SIZE: A4	SHEET:10F 1
CUSTOMER COPY					