



REV.	ECN NO OR DESCRIPTION	REVISED	DATE

NOTES

MATERIAL

1. HOUSING MATERIAL: THERMO PLASTICS UL94V-0.
2. CONTACT MATERIAL: PHOSPHOR BRONZE $\phi 0.46\text{mm}$.
3. PLATING : GOLD FLASH PLATING OVER NICKEL.
4. SHELL : BRASS, T=0.2 NICKEL PLATED.

ELECTRICAL

1. VOLTAGE RATING: 125 VAC RMS.
2. CURRENT RATING: 1.5 AMP.
3. CONTACT RESISTANCE :40 MILLIOHMS MAX.
4. INSULATION RESISTANCE:500 MEGOHMS MIN @ 100V DC .
5. DIELECTRIC DIELECTRIC RESISTANCE : 500V DC RMS 50Hz. 1MIN.

MECHANICAL

1. DURRABILITY : 750 CYCLES MIN.
2. MATING/UNMATING FORC: 2.24 KG.F MAX.

ENVIRONMENTAL:


1. OPERATION: $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$.
2. STORAGE: $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$.

RJ5524 - 042 - XX

系列码

类别码
5524无耳
流水码
11:有壳GF PBT黑盘装
12:有壳GF PBT黄盘装

UNLESS OTHERWISE SPECIFIED TOLERANCES		东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD			
DECIMALS:	ANGLES:	TITLE	5524 1x2立式有壳DIP脚		
X : ± 0.30	X : $\pm 2^{\circ}$	DWN	xiong	PART NO. RJ5524-042-11	
X.X : ± 0.20	X.X : $\pm 1^{\circ}$	CHKD	lee	SCALE:1:1	UNIT: mm
X.XX : ± 0.10		APVD	wang	SIZE: A4	SHEET:10F 1
CUSTOMER COPY					
REV: A4					



PCBLAYOUT
TOL: ± 0.05