








P.C.B RECOMMENDED HOLE LAYOUT
SEEN FROM COMPONENT SIDE.

NOTES:

MATERIAL

- 1.HOUSING MATERIAL: THERMOPLASTIC BLACK UL94V-0.
- 2.CONTACT MATERIAL: C5191 R-H T=0.3MM
- 3.SHELL: SUS304 T=0.2MM

FINISH:

- 1.CONTACT PLATING: GOLD PLATING OVER NICKEL.

ELECTRICAL:

- 1.VOLTAGE RATING:125 VAC RMS
- 2.CURRENT RATING:1.5 AMP
- 3.CONTACT RESISTANCE: 30 MILLIOHMS MAX
- 4.INSULATION RESISTANCE: 500 MEGOHMS MIN @ 500V DC
- 5.DIELECTRIC WITHSTANDING VOLTAGE :500V AC R.M.S MIN

MECHANICAL:

- 1.DURRABILITY: 750 CYCLES MIN

LED ELECTRICAL CHARACTERISTIC			
Orange		Green	
9-10		11-12	
LEFT LED		RIGHT LED	

Standard LED	Wavelength	Forward V (Min/Max)	Forward A	Type
Green	568nm	1.8v/2.8v	20mA	squareness
Yellow	585nm	1.8v/2.8v	20mA	squareness
Orange	610nm	1.8v/2.8v	20mA	squareness

UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS: ANGLES:
X :±0.35 X :±2°
X.X :±0.25 X.X :±1°
X.XX :±0.15



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

TITLE	RJ45 沉板式9.9H板上4.3H带灯 左橙右绿			
DWN	xiong	PART NO.	RJ45-881A11-2	
CHKD	lee	SCALE:1:1	UNIT: mm	
APVD	wang	SIZE: A4	SHEET:10F 1	REV: A4

CUSTOMER COPY