






ROHS compliant



NOTES:

1.MECHANICAL:

- 1>.Operation force: 1000gf Max.
- 2>.Operation Temperature: -30 °C to +85 °C.
- 3>.Storage Temperature: -40 °C to +85 °C.
- 4>.Mechanical Life: 3000 cycles operations.
- 5>.Resistance to Soldering: 260 ±5°C for 3-5 Seconds.
- 6>.Please keep switch in "OFF" when welding.

2.MATERIAL:


- 1>.Base: UL94V-0 PBT Thermoplastic / Color:Black.
2>.COVER: UL94V-0 PBT Thermoplastic / Color:Red,
Black, Blue.
3>.ACTUATOR: UL94V-0 PBT High Thermoplastic /
Color: White.
4>.TERMINAL: Copper alloy with gold plating for1.5u".

3.ELECTRICAL:

- 1> Non-switching Rating: 100mA at 50VDC.
- 2> Switching Rating: 25mA at 24VDC.
- 3> Contact Resistance: Initial 50m Ω **Max.**
Contact Resistance: After life 100m Ω Max.
- 4> Insulation Resistance: 100M Ω Min at 500VDC.
- 5> Dielectric Strength: 500VAC for 60seconds.
- 6> Switch Capacitance: 5PF Max at 1MHZ.

4.PART NUMBER DESCRIPTION:

DA-XX-K-T



5.PACKING: 53pcs/Tube, 2120pcs/Box.

Drawing		DKG	Date	2018. 01. 20	LINER	ANGLES	PRODUCT Family DA Series Pitch 2.54mm	
Check	TOM	Scale	3 : 1	>0±0. 05	>0° ±0. 5°	PRAT NO.	DA-03-K-T	
Approved		Unit	MM	>1±0. 10	>5° ±1. 0°	FILE NO.	SK-DA-003-K	
Size	A4	Rev.	A	>10±0. 30		PROJECTION		
东莞市康深电子科技有限公司 Kongshen Electronics technology co., LTD.								