





- SPECIFICATIONS
- 1、Current Rating: 23A AC, DC
 - 2、Voltage Rating: 600V AC, DC
 - 3、Temperatuer Range: -40℃~ +105℃
 - 4、Contact Resistance: 10mΩ Max
 - 5、Insulation Resistance: 1000mΩ Min
 - 6、Withstanding Voltang: 2200V AC/minute
 - 7、Material: Housing Nylon66, UL94-V0(2)

Circuit	Part NO.	Dimensions mm	
		A	B
1	HC-5557C-2x1Y-05	---	8.35
2	HC-5557C-2x2Y-05	5.70	12.05
3	HC-5557C-2x3Y-05	11.40	17.75
4	HC-5557C-2x4Y-05	17.10	23.45
5	HC-5557C-2x5Y-05	22.80	29.15
6	HC-5557C-2x6Y-05	28.50	34.85
7	HC-5557C-2x7Y-05	34.20	40.55
8	HC-5557C-2x8Y-05	39.90	46.25
9	HC-5557C-2x9Y-05	45.60	51.95
10	HC-5557C-2x10Y-05	51.30	57.65

Ordering Information



			GENEERL TOLERANCE	制 图 DRAWING		 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM TOL	审 核 CHECK					
			X.X ±0.30	批 准 APPROVAL		产品名称 TITLE	5557C (5.70) 双排 带扣孔座	版 本 REV.	A
1	初版发行		X.XX ±0.20	比 例 SCALE		产品料号 PART NO.	HC-5557C-2xNY-05	单 位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日 期 MODIFY DATE	X.XXX ±0.10	投 影 Projection		材 料 MATERIAL		页 次 SHEET	1/1
			Angle ±3.0°						