




RECOMMEND P. C. B LAYOUT
PCB TOLERANCE: ±0.05 (TOP VIEW)

SPECIFICATIONS

Current Rating: 1.0 Amps
Withstanding Voltage: AC 500V
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Operation Temperature: -40°to+105°
Insulator Material: Polyester(UL94V-0)
Contact Material: Phosphor bronze
Standard: PA6T
Contact Plating: Gold Flash
Max. Processing Temp: 240°C for 30-60 seconds
(260°C for 5 seconds)

HB-FH 7-127 XXX X X XX X - XXX

- Series No:
FH-Pin Header
- Welding Board Type:
7-双排SMT/SMT
TYPE
- Pitch:
100-1.00mm
127-1.27mm
200-2.00mm
254-2.54mm
- PIN位/PIN bit:
2*1P=21P
- 颜色/Color:
B-Black
- 材料/Material:
1-PBT 2-PA6T
- 触点电镀/Contact Plating:
G0-Gold Flash
- 包装方式/Package Type:
P-袋装/PE B-盒装/BOX
T-管装/Tubing W-卷装/winding
- 其他备注/Other remarks

CSG PART NO.	No. of	DIM. A	DIM. B	CSG PART NO.	No. of	DIM. A	DIM. B
HB-FH7-12721PB2GOT	2*1P	—	—	HB-FH7-127226PB2GOT	2*26P	31.75	33.02
HB-FH7-12722PB2GOT	2*2P	1.27	2.54	HB-FH7-127227PB2GOT	2*27P	33.02	34.29
HB-FH7-12723PB2GOT	2*3P	2.54	3.81	HB-FH7-127228PB2GOT	2*28P	34.29	35.56
HB-FH7-12724PB2GOT	2*4P	3.81	5.08	HB-FH7-127229PB2GOT	2*29P	35.56	36.83
HB-FH7-12725PB2GOT	2*5P	5.08	6.35	HB-FH7-127230PB2GOT	2*30P	36.83	38.10
HB-FH7-12726PB2GOT	2*6P	6.35	7.62	HB-FH7-127231PB2GOT	2*31P	38.10	39.37
HB-FH7-12727PB2GOT	2*7P	7.62	8.89	HB-FH7-127232PB2GOT	2*32P	39.37	40.64
HB-FH7-12728PB2GOT	2*8P	8.89	10.16	HB-FH7-127233PB2GOT	2*33P	40.64	41.91
HB-FH7-12729PB2GOT	2*9P	10.16	11.43	HB-FH7-127234PB2GOT	2*34P	41.91	43.18
HB-FH7-127210PB2GOT	2*10P	11.43	12.70	HB-FH7-127235PB2GOT	2*35P	43.18	44.45
HB-FH7-127211PB2GOT	2*11P	12.70	13.97	HB-FH7-127236PB2GOT	2*36P	44.45	45.72
HB-FH7-127212PB2GOT	2*12P	13.97	15.24	HB-FH7-127237PB2GOT	2*37P	45.72	46.99
HB-FH7-127213PB2GOT	2*13P	15.24	16.51	HB-FH7-127238PB2GOT	2*38P	46.99	48.26
HB-FH7-127214PB2GOT	2*14P	16.51	17.78	HB-FH7-127239PB2GOT	2*39P	48.26	49.53
HB-FH7-127215PB2GOT	2*15P	17.78	19.05	HB-FH7-127240PB2GOT	2*40P	49.53	50.80
HB-FH7-127216PB2GOT	2*16P	19.05	20.32	HB-FH7-127241PB2GOT	2*41P	50.80	52.07
HB-FH7-127217PB2GOT	2*17P	20.32	21.59	HB-FH7-127242PB2GOT	2*42P	52.07	53.34
HB-FH7-127218PB2GOT	2*18P	21.59	22.86	HB-FH7-127243PB2GOT	2*43P	53.34	54.61
HB-FH7-127219PB2GOT	2*19P	22.86	24.13	HB-FH7-127244PB2GOT	2*44P	54.61	55.88
HB-FH7-127220PB2GOT	2*20P	24.13	25.40	HB-FH7-127245PB2GOT	2*45P	55.88	57.15
HB-FH7-127221PB2GOT	2*21P	25.40	26.67	HB-FH7-127246PB2GOT	2*46P	57.15	58.42
HB-FH7-127222PB2GOT	2*22P	26.67	27.94	HB-FH7-127247PB2GOT	2*47P	58.42	59.69
HB-FH7-127223PB2GOT	2*23P	27.94	29.21	HB-FH7-127248PB2GOT	2*48P	59.69	60.96
HB-FH7-127224PB2GOT	2*24P	29.21	30.48	HB-FH7-127249PB2GOT	2*49P	60.96	62.23
HB-FH7-127225PB2GOT	2*25P	30.48	31.75	HB-FH7-127250PB2GOT	2*50P	62.23	63.50

UNLESS OTHERWISE SPECIFIED TOLERANCES		东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD			
DECIMALS:	ANGLES:	TITLE	127 FH H4.3 2xnPin 双排SMT 型 PC4.8 PB4.6 PA6T		
X : ±0.30	X : ±2°	DWN	xiong	PART NO.	HB-FH7-127XXXXB2GOT
X.X : ±0.25	X.X : ±1°	CHKD	lee	SCALE: 1:1	UNIT: mm
X.XX : ±0.20		APVD	wang	SIZE: A4	SHEET: 10F 1
CUSTOMER COPY					