



REV.	ECN NO OR DESCRIPTION	REVISED	DATE

NOTES:

1. MATERIAL:

1.1 HOUSING: LCP BLACK UL94V-0

1.2 CONTACT: C5191-EH T=0.3

1.3 SHELL: SUS201 T=0.2

2. FINISH:

2.1 CONTACT:


Au 3u" PLATED ON CONTACT AREA

Sn PLATED ON SOLDER TAIL AREA



NI 30' min UNDER PLATING OVERALL

2.2 SHELL 50u" NICKEL UNDER PLATING OVERALL

3. OTHER GENERAL SPEC TO REFER: RJ45 SERIES SPEC



RECOMMENDED PCB LAYOUT(TOP VIEW)
GENERAL TOLERANCES: ±0.05



3	SHELL	SUS201	Ni Plated	1pcs
2	TERMINAL	C5191-EH	Au/Ni Plated	8pcs
1	HOUSING	LCP UL 94V-0	BLACK	1pcs
No.	DESCRIPTION	MATERIAL	REMARKS	Q.TY

UNLESS OTHERWISE
SPECIFIED TOLERANCES



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

DECIMALS: ANGLES:
X :±0.35 X :±2°
X.X :±0.25 X.X :±1°
X.XX :±0.15

TITLE	RJ45 8P8C SMT 1x1 PORT 扁针			
DWN	xiong	PART NO. RJ45-893-810		
CHKD	lee	SCALE: 1:1	UNIT: mm	
APVD	wang	SIZE: A4	SHEET: 10F 1	

CUSTOMER COPY