



焊脚尺寸以顺畅过孔规为准

NOTES

MATERIAL

1. HOUSING MATERIAL: GLASS FILLED POLYESTER UL94V-0.
2. CONTACT MATERIAL: PHOSPHOR BRONZE $\phi 0.46\text{mm}$.
3. PLATING: GOLD FLASH PLATING OVER NICKEL.
4. SHIELD: BRASS TO .20mm 40u" NICKEL PLATED.

ELECTRICAL



1. VOLTAGE RATING: 125 VAC RMS.
2. CURRENT RATING: 1.5 AMP.
3. CONTACT RESISTANCE: 40 MILLIOHMS MAX.
4. INSULATION RESISTANCE: 500 MEGOHMS MIN @ 100V DC .
5. DIELECTRIC RESISTANCE: 500V DC RMS 50Hz. 1MIN.

MECHANICAL

1. DURRABILITY: 750 CYCLES MIN.
2. MATING/UNMATING FORCE: 2.24 KG.F MAX.

ENVIRONMENTAL:

1. STORAGE: $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$.
2. OPERATION: $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$.



UNLESS OTHERWISE SPECIFIED TOLERANCES		东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD			
DECIMALS:	ANGLES:	TITLE	RJ45 56B型带弹左黄右绿DIP-0.5u'淡PBT黑		
X : ± 0.30	X : $\pm 2^{\circ}$	DWN	xiong	PART NO. RJ3202-009-05	
X.X : ± 0.20	X.X : $\pm 1^{\circ}$	CHKD	lee	SCALE: 1:1	UNIT: mm
X.XX : ± 0.10		APVD	wang	SIZE: A4	SHEET: 10F 1
		REV: A4			
		CUSTOMER COPY			