











2x7~2x10 Pin




2x4~2x6 Pin



2x12 Pin



2x14 Pin以上



SPECIFICATIONS

- 1、Current Rating: 3mA AC, DC
- 2、Voltage Rating: 12V AC, DC
- 3、Temperatuer Range: -40℃~ +105℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 100mΩ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material: Wafer PBT UL94-V0
PIN Brass Tin-plated

Circuit	Part NO.	Dimensions mm		
		A	B	C
4	HC-QA-2x4AW-05	6.60	14.20	8.20
5	HC-QA-2x5AW-05	8.80	16.40	9.50
6	HC-QA-2x6AW-05	11.00	18.60	9.60
7	HC-QA-2x7AW-05	13.20	20.80	11.80
8	HC-QA-2x8AW-05	15.40	23.00	14.00
9	HC-QA-2x9AW-05	17.60	25.20	16.20
10	HC-QA-2x10AW-05	19.80	27.40	21.50
12	HC-QA-2x12AW-05	24.20	31.80	23.10
14	HC-QA-2x14AW-05	28.60	36.20	27.20
16	HC-QA-2x16AW-05	33.00	40.60	31.60
20	HC-QA-2x20AW-05	41.80	49.40	40.40

Ordering Information

HC-QA - N*** - * - 05

Pin Type Colour
Y=孔座 AW=弯针
默认=本色
R=红色
L=蓝色
B=黑色
Y=黄色
P=紫色
V=绿色
G=棕色
BR=棕色

			GENERAL TOLERANCE		制图 DRAWING	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	审核 CHECK				
			X.X	±0.30	批准 APPROVAL	产品名称 TITLE	QA (2.20) 双排 弯针	版本 REV.	A
1	初版发行		X.XX	±0.20	比例 SCALE	产品料号 PART NO.	HC-QA-2xNAW-05	单位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	X.XXX	±0.10	投影 Projection	材料 MATERIAL		页次 SHEET	1/1
			Angle	±3.0°					