





REV.	ECN NO OR DESCRIPTION	REVISED	DATE

NOTES

- MATERIAL
- 1. HOUSING MATERIAL: PA46 BLACK UL94V-0.
 - 2. CONTACT MATERIAL: PHOSPHOR BRONZE $\phi 0.46\text{mm}$.
 - 3. PLATING: GOLD FLASH PLATING .
 - 4. SHELL: BRASS T=0.2mm NI PLATING.
- ELECTRICAL
- 1. VOLTAGE RATING: 125 VAC RMS.
 - 2. CURRENT RATING: 1.5 AMP.
 - 3. CONTACT RESISTANCE: 40 MILLIOHMS MAX.
 - 4. INSULATION RESISTANCE: 500 MEGOHMS MIN @ 100V DC .
 - 5. DIELECTRIC DIELECTRIC RESISTANCE: 500V DC RMS 50Hz. 1MIN.
- MECHANICAL
- 1. DURRABILITY: 750 CYCLES MIN.
 - 2. MATING/UNMATING FORCE: 2.24 KG.F MAX.
- ENVIRONMENTAL:
- 1. STORAGE: $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$.
 - 2. OPERATION: $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$.



RJ45-401-32-11

流水码
11: PA46 黑色

类别码
32: 有壳左绿右黄 B3.85

PCBLAYOUT
TOL: ±0.05

UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS: ANGLES:
X : ±0.35 X : ±2°
X.X : ±0.25 X.X : ±1°
X.XX : ±0.15



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

TITLE	RJ45 52立式有壳左绿右黄 B3.85 DIP			
DWN	xiong	PART NO. RJ45-401-32-11		
CHKD	lee	SCALE: 1:1	UNIT: mm	
APVD	wang	SIZE: A4	SHEET: 10F 1	REV: A4

CUSTOMER COPY