





REV.	ECN NO OR DESCRIPTION	REVISED	DATE



SPECIFICATION NOTES:

ELECTRICAL:

1. VOLTAGE RATING: 125 VAC RMS
2. CURRENT RATING: 1.5 AMP
3. CONTACT RESISTANCE: 30mΩ MAX.
4. INSULATION RESISTANCE: 500MΩMIN. AT 500V DC.
5. DIELECTRIC STRENGTH: 1000 VAC 50Hz 1MINUTE

MECHANICAL:

1. HOUSING MATERIAL:
SEE PART NUMBER.
2. CONTACTS: φ0.46mm PHOSPHOR BRONZE, GOLD PLATING OVER NICKEL
3. SHIELD: 0.20mm THICKNESS COPPER ALLOY WITH NICKEL PLATED.
4. OPERATING LIFE: 750 CYCLES MIN.
5. MATING FORCE: 30N MAX.
UNMATING FORCE: 30N MAX.

ENVIRONMENTAL:

1. STORAGE: -40°C TO +85°C
2. OPERATION: -40°C TO +85°C

Recommend PCB Layout
(Jack Top View)
TOLERANCES: ±0.05

UNLESS OTHERWISE SPECIFIED TOLERANCES		 东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD			
DECIMALS:	ANGLES:	TITLE	RJ45 5J 8P8C全包无灯无弹		
X : ±0.35	X : ±2°	DWN	xiong	PART NO. RJ45J-11881A15-A	
X.X : ±0.25	X.X : ±1°	CHKD	lee	SCALE: 1:1	UNIT: mm
X.XX : ±0.15		APVD	wang	SIZE: A4	SHEET: 10F 1
CUSTOMER COPY					