




REV.	ECN NO OR DESCRIPTION	REVISED	DATE



RECOMMEND P. C. B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

SPECIFICATIONS

Current Rating:1.0 Amps
Withstanding Voltage: AC 500V
Insulation Resistance:1000MQ Min
Contact Resistance:20mΩ Max
Operation Temperature:-40*to+105°
Insrlator Material:Polyester(UL94V-0)
Standard:PA6T
Contact Plating:Gold Flash
Max.Processing Temp: 240°C for30-60seconds
(260°C for5seconds)

HB-FH 2-127 XXX X X XX X - XXX
1 2 3 4 5 6 7 8 9

- Series No:
FH-Pin Header
- Welding Board Type:
2-180度单排插件/DIP
TYPE
- Pitch:
100-1.00mm
127-1.27mm
200-2.00mm
254-2.54mm
- PIN位/PIN bit:
1*1P=11P
- 颜色/Color:
B-Black
- 材料/Material:
1-PBT 2-PA6T
- 触点电镀/Contact Plating:
G0-Gold Flash
- 包装方式/Package Type:
P-袋装/PE B-盒装/BOX
T-管装/Tubing W-卷装/winding
- 其他备注/Other remarks

CSG PART NO.	No. of	DIM. A	DIM. B	CSG PART NO.	No. of	DIM. A	DIM. B
HB-FH2-12711PB2GOB	1*1P	—	—	HB-FH2-127126PB2GOB	1*26P	31.75	33.02
HB-FH2-12712PB2GOB	1*2P	1.27	2.54	HB-FH2-127127PB2GOB	1*27P	33.02	34.29
HB-FH2-12713PB2GOB	1*3P	2.54	3.81	HB-FH2-127128PB2GOB	1*28P	34.29	35.56
HB-FH2-12714PB2GOB	1*4P	3.81	5.08	HB-FH2-127129PB2GOB	1*29P	35.56	36.83
HB-FH2-12715PB2GOB	1*5P	5.08	6.35	HB-FH2-127130PB2GOB	1*30P	36.83	38.10
HB-FH2-12716PB2GOB	1*6P	6.35	7.62	HB-FH2-127131PB2GOB	1*31P	38.10	39.37
HB-FH2-12717PB2GOB	1*7P	7.62	8.89	HB-FH2-127132PB2GOB	1*32P	39.37	40.64
HB-FH2-12718PB2GOB	1*8P	8.89	10.16	HB-FH2-127133PB2GOB	1*33P	40.64	41.91
HB-FH2-12719PB2GOB	1*9P	10.16	11.43	HB-FH2-127134PB2GOB	1*34P	41.91	43.18
HB-FH2-127110PB2GOB	1*10P	11.43	12.70	HB-FH2-127135PB2GOB	1*35P	43.18	44.45
HB-FH2-127111PB2GOB	1*11P	12.70	13.97	HB-FH2-127136PB2GOB	1*36P	44.45	45.72
HB-FH2-127112PB2GOB	1*12P	13.97	15.24	HB-FH2-127137PB2GOB	1*37P	45.72	46.99
HB-FH2-127113PB2GOB	1*13P	15.24	16.51	HB-FH2-127138PB2GOB	1*38P	46.99	48.26
HB-FH2-127114PB2GOB	1*14P	16.51	17.78	HB-FH2-127139PB2GOB	1*39P	48.26	49.53
HB-FH2-127115PB2GOB	1*15P	17.78	19.05	HB-FH2-127140PB2GOB	1*40P	49.53	50.80
HB-FH2-127116PB2GOB	1*16P	19.05	20.32	HB-FH2-127141PB2GOB	1*41P	50.80	52.07
HB-FH2-127117PB2GOB	1*17P	20.32	21.59	HB-FH2-127142PB2GOB	1*42P	52.07	53.34
HB-FH2-127118PB2GOB	1*18P	21.59	22.86	HB-FH2-127143PB2GOB	1*43P	53.34	54.61
HB-FH2-127119PB2GOB	1*19P	22.86	24.13	HB-FH2-127144PB2GOB	1*44P	54.61	55.88
HB-FH2-127120PB2GOB	1*20P	24.13	25.40	HB-FH2-127145PB2GOB	1*45P	55.88	57.15
HB-FH2-127121PB2GOB	1*21P	25.40	26.67	HB-FH2-127146PB2GOB	1*46P	57.15	58.42
HB-FH2-127122PB2GOB	1*22P	26.67	27.94	HB-FH2-127147PB2GOB	1*47P	58.42	59.69
HB-FH2-127123PB2GOB	1*23P	27.94	29.21	HB-FH2-127148PB2GOB	1*48P	59.69	60.96
HB-FH2-127124PB2GOB	1*24P	29.21	30.48	HB-FH2-127149PB2GOB	1*49P	60.96	62.23
HB-FH2-127125PB2GOB	1*25P	30.48	31.75	HB-FH2-127150PB2GOB	1*50P	62.23	63.50

UNLESS OTHERWISE SPECIFIED TOLERANCES		东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD			
DECIMALS:	ANGLES:	TITLE	127 FH H4.3 1xPin 180度 W2.1 U型 PC2.4 PA6T		
X :±0.30	X :±2°	DWN	xiong	PART NO. HB-FH2-127XXXXB2GOB	
X.X :±0.25	X.X :±1°	CHKD	lee	SCALE:1:1	UNIT: mm
X.XX :±0.20		APVD	wang	SIZE: A4	SHEET:1OF 1
CUSTOMER COPY					