





NOTES

MATERIAL

1. HOUSING MATERIAL : THERMO PLASTICS UL94V-0.
2. CONTACT MATERIAL : PHOSPHOR BRONZE $\phi 0.46\text{mm}$.
3. PLATING : GOLD FLASH PLATING OVER NICKEL.
4. SHIELD : 0.20mm THICKNESS COPPER ALLOY WITH NICKEL PLATED.

ELECTRICAL



1. VOLTAGE RATING : 125 VAC RMS.
2. CURRENT RATING : 1.5 AMP.
3. CONTACT RESISTANCE : 40 MILLIOHMS MAX.
4. INSULATION RESISTANCE : 500 MEGOHMS MIN @ 100V DC .
5. DIELECTRIC DIELECTRIC RESISTANCE : 500V DC RMS 50Hz. 1MIN.

MECHANICAL

1. DURABILITY : 750 CYCLES MIN.
2. MATING/UNMATING FORC: 2.24 KG.F MAX.

ENVIRONMENTAL:

1. OPERATION : $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$.
2. STORAGE : $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$.



PCBLAYOUT
TOL: ± 0.05

PART NUMBER DESCRIPTION:

RJ45-505-XX7-XX

类别码

01:56S

流水码

33:无弹左黄右绿GF PBT黑盘装

MANUFACTURE DWG



东莞市讯普电子科技有限公司
DongGuan XunPu Electronics Co.,Ltd

UNLESS OTHERWISE
SPECIFIED TOLERANCES



TITLE:

56S 1x2无弹左黄右绿DIP GF PBT黑

PAR

RJ45-505-017-33

DECIMALS:

.X: ± 0.35

.XX: ± 0.25

.XXX: ± 0.15

ANGLES:

X' : $\pm 3^{\circ}$

.X' : $\pm 2^{\circ}$

.XX' : $\pm 1^{\circ}$

DWN

CHKD

APVD

SCALE 1:1

UNIT:MM

SIZE:A4

SHEET:1F1

REV:A

CUSTOMER COPY

REV:A