

NOTES

MATERIAL

1.HOUSING MATERIAL : THERMO PLASTICS
UL94V-0.

2.CONTACT MATERIAL : PHOSPHOR BRONZE
Ø0.46mm.

3.PLATING : GOLD FLASH PLATING
OVER NICKEL.

4.SHIELD : 0.20mm THICKNESS
COPPER ALLOY WITH NICKEL PLATED.

ELECTRICAL

1.VOLTAGE RATING : 125 VAC RMS.

2.CURRENT RATING : 1.5 AMP.

3.CONTACT RESISTANCE : 40 MILLIOHMS MAX.

4.INSULATION RESISTANCE : 500 MEGOHMS MIN @
100V DC

5.DIELECTRIC DIELECTRIC
RESISTANCE : 500V DC RMS 50Hz.
1MIN.

MECHANICAL


1.DURRABILITY : 750 CYCLES MIN.

2. MATING/UNMATING FORC: 2.24 KG.F MAX.

ENVIRONMENTAL

1.OPERATION : -40℃~+85℃.

2.STORAGE : -40℃~+85℃.




PART NUMBER DESCRIPTION:

RJ45-541-XX4-XX

类别码 03:56S 1X4

流水码 44:无弹左黄右绿GF PA46黑盘装



PCBLAYOUT
TOL:±0.05

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: 56S 1x4 无弹左黄右绿有后脚 GF PA46黑
DECIMALS:	ANGLES:		PAR RJ45-541-034-44
.X:±0.35	X'.:±3'		DWN
.XX:±0.25	.X':±2'		CHKD
.XXX:±0.15	.XX':±1'	APVD	SCALE:1:1 UNIT:MM
CUSTOMER COPY		SIZE:A4	SHEET:1F1 REV:A