






MATERIAL
1.HOUSING MATERIAL : THERMO PLASTICS UL94V-0.
2.CONTACT MATERIAL : PHOSPHOR BRONZE Ø0.46mm.
3.PLATING : GOLD FLASH PLATING OVER NICKEL.
4.SHIELD : BRASS T=0.20mm WITH NICKEL PLATED.
ELECTRICAL
1.VOLTAGE RATING : 125 VAC RMS.
2.CURRENT RATING : 1.5 AMP.
3.CONTACT RESISTANCE : 40 MILLIOHMS MAX.
4.INSULATION RESISTANCE : 500 MEGOHMS MIN @ 100V DC .
5.DIELECTRIC DIELECTRIC RESISTANCE : 500V DC RMS 50Hz. 1MIN.
MECHANICAL
1.DURRABILITY : 750 CYCLES MIN.
2. MATING/UNMATING FORC: 2.24 KG.F MAX.
ENVIRONMENTAL:
1.OPERATION : -40℃~+85℃.
2.STORAGE : -40℃~+85℃.



PCBLAYOUT
TOL:±0.05

YELLOW GREEN

DOWN LEFT DOWN RIGHT

RJ45-604-023-XX

流水码
O1:带弹左黄右绿 GF PA46黑盘装

— 类别码

MANUFACTURE DWG		 东莞市讯普电子有限公司 DongGuan XunPu Electronics Co.,Ltd			
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: RJ45 2x4带弹左黄右绿DIP P16.26		
			PAR	RJ45-604-023-01	
DECIMALS:	ANGLES:		DWN		
.X:±0.35	X":.±3"		CHKD		
.XX:±0.25	.X":±2"		APVD		
.XXX:±0.15	.XX":±1"		SCALE 1:1	UNIT:MM	
		CUSTOMER COPY	SIZE:A4	SHEET:1F1	REV:A