




Model No.	POS.1	POS.2
8BS8	ON 	MOM 
Term. Comm.	2-1	2-3
SCHEMATIC		

SWITCH FUNCTION

本公司智慧財產，未經同意不得複製
DAILYWELL copyright, may not be used
without permission from DAILYWELL



SPECIFICATIONS

MECHANICAL LIFE: 50,000 make-and-break cycles.
CONTACT RESISTANCE: 20m Ω max. initial @ 24VDC
 100mA for both silver and gold plated contacts
INSULATION RESISTANCE: 1,000M Ω min.
DIELECTRIC STRENGTH: 1,000 V RMS@sea level.
OPERATING TEMPERATURE: -30°C to 85°C.

MATERIALS

CASE & BUSHING - Glass filled nylon 66, flame retardand, heat stabilized (UL94V-0).

PLUNGER - Thermoplastic Polyester (UL 94V-0), with internal O-ring seal

SWITCH SUPPORT - Brass or steel electrotin plated.

CONTACT - Silver or gold plated Copper alloy.

RoHS - 2002/95/EC

徳

	符號	原尺寸	修改後尺寸	變更日期	SCALE (比例) : 3 : 2				TITLE	Sealed Sub - Miniature Pushbutton Switches(SMT)				SIZE	
1	Ⓐ-1	10.23(.403)	10.16(.400)	MAR-10-2010	TOLERANCE (公差) : 0.00 mm ± 0.25mm				DWG NO. 圖 號	8BS8MZQES				圖紙	A4
2	Ⓐ-2	9.00(.354)	7.95(.313)	MAR-10-2010										UNIT	inch
3	Ⓑ				0.0 mm ± 0.40mm				REV. 版 本	DATE	JUL - 15 - 2008	SHEET	1 of 1		
4	Ⓒ													B	日期
5	Ⓓ				ANGULAR : ± 5°				CHECKED BY	RICHARD		DRAWN BY	IRENE		
					FILE NAME : 8BSP0044				審 核			製 圖			

德利威電子股份有限公司
DAILYWELL ELECTRONICS CO.,LTD.