





说明:

- 1.胶芯:LCP黑色;UL94V-0.
- 2.端子:C2680 T=0.15mm,半金镍G/F (功能区)
- 3.外壳:C2680 T=0.25mm,镀锡
- 4.额定电流:1A 最大.
- 5.耐电压:100V(AC)/1分钟 至少.
- 6.接触阻抗:50mΩ 最大.
- 7.绝缘阻抗:100MΩ 最小.
- 8.插入力:3.57Kgf 最大.
- 9.拔出力:1.0Kgf初始 最小;测试后0.81Kgf 最小
- 10.温度范围:-30°C~+80°C

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE:Micro usb 5s 6.4有焊脚有柱
DECIMALS:	ANGLES:		PAR MU-103-ACY64
.X:±0.25	X.:±2°		DWN Lucas
.XX:±0.10	X.X':±0.5°		CHKD Ethan
.XXX:±0.05		CUSTOMER COPY	APVD Jacob
		SIZE:A4	SCALE1:1 UNIT:MM
		SHEET:1F1	REV:A



说明:

- 1, 将检查合格的产品, 放入承载带中, 一盘包装1000/1500PCS;
- 2, 将15盘承载带放入纸箱中;
- 3, 将纸箱封装好, 贴上标签。

每箱数量	净重(Kg)	毛重(Kg)
15000/22500PCS	XXX	XXX

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co., Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES		 TITLE:Micro usb 5s 6.4有焊脚有柱	
DECIMALS:	ANGLES:	PAR	MU-103-ACY64
.X:±0.25	X.'':±2°	DWN	Lucas
.XX:±0.10	X.X':±0.5°	CHKD	Ethan
.XXX:±0.05		APVD	Jacob
CUSTOMER COPY		SCALE:1:1	UNIT:MM
		SIZE:A4	SHEET:1F1
			REV:A