


1 2 3 4 5 6 7 8

REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	WPY 11/14/24'		

晨翔2.0mm TJC8 TYPE 黑色1*14pin胶芯

晨翔料号: I-DS1071-01-SCB01x14

DC 1
ED 1
FE 1
ISO 1
PD 1
R&D 1
SD 1
QA 1
QC 1
QE 1

1. 电性说明:
1.1 耐压: 500伏交流电一分钟
1.2 绝缘阻抗: 500兆欧最小
1.3 额定电流: 2安
2. 环境特性:
2.1 工作温度: -25~+85° C
3. 材料:
3.1 胶芯: PA66, 黑色
4. 产品符合欧盟RoHS环保要求

2.0mm TJC8 TYPE 黑色1*14pin胶芯

晨翔电子有限公司

CONNPLY CONNPLY ELECTRONIC CO. LTD

26.00
28.30±0.3

7.23

2.16

GENERAL TOLERANCE

X.	±0.60
.X	±0.38
.XX	±0.25

ANGLE TOLERANCE

X.	±5°
.X	±3°
.XX	±2°

DRAWING TYPE

CUSTOMER

SCALE

1:1

SHEET

1 OF 1

DRAWING NO.

C-DS1071-01-XXXXX-A

PROJECTION

UNITS

mm

SHEET SIZE

A4

TITLE

2.0mm TJC8 TYPE 黑色1*14pin胶芯

SERIES

DS1071-01 SERIES