

NOTES1:

UL Standard

- 1.Rated voltage/current : 150V / 8A
- 2.Withstanding voltage : AC1500V/1Min.
- 3.Wire range : 26~16AWG

IEC Standard

1.	Pollution degree	2
	Overvoltage category	III
	Rate impulse voltage(KV)	2.5KV
	Rate voltage(V)	160V
	Rate current(A)	8A

NOTES2:

- 1.Dimension shall be interpreted per ASME Y14.5-2009
- 2.Pitch : 3.5mm, Poles : N=04~48P(Total)
- 3.Stripping length : 9-10mm
- 4.Operating temperature: -40°C~+105°C
- 5.Undimensioned tolerances:

Pitch range in mm			Nominal dimension range in mm									
TO 6	Over 6 TO 10	Over 10 TO 24	TO 30	Over 30 TO 60	Over 60 TO 100	Over 100 TO 150	Over 150			0.1/10		
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±1.30	±2*				

6.RoHS Compliance

Ordering Information





JL15EDGKNH - 350 XX X XX

Pitch 350=3.5PH


No.of pins 2*2P~2*24P
02=2*2P
03=2*3P
04=2*4P
...

Housing Color B=Black (Convention)
G=Green
U=Blue
R=Red
W=White
Y=Yellow
O=Orange
E=Grey

Serial code



2*2P-2*6P加筋条



DRAW	SHUANGPING ZHENG	SCALE	FIT	JILN ® 东莞市锦凌电子有限公司 DONGGUAN JINLING ELECTRONIC CO.,LTD	
CHECK	LICHAO LIU	UNIT	mm		
		SIZE	A4		
		SHEET	1/1		
APPROVE	YONGLIANG GAO	PROJ.	Φ	PART NO.	JL15EDGKNH-350XXXXX
			TITLE:	JL15EDGKNH-3.5-2*XXP插拔式母座	

4	Shrapnel	SUS 301	/
3	Handle	POM	/
2	Contact	Copper alloy	Sn plated
1	Housing	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES