




技术参数:
间距: 7.2*17.7MM
额定电流: 80-100A
压线螺钉: M4/M5
焊接端子: Brass, Tin Plated
螺钉扭矩: 18lbf. in

东莞市博众电气有限公司 DONGGUAN BOZHONG ELECTRIC CO., LTD 品名 (ITEM NO) 料号 (PART NO) 图号 (DWG NO) M4黄铜镀雾锡贴片 焊脚端子 BTC22M4NBB4SCM		页码 (SHEET)	1/1	单位 (UNIT): MM
		版本 (REV)	A1	比例 (SCALE)
		日期 (DATE)	2021. 10. 12	
		设计 (DESIGN)	LUO	未注公差 TOLERANCE UNSPECIFIED
		审核 (CHECKED)	ROGER LI	X. ±0.20 X.* ±4*
		核准 (APPROVED)	ROC ZHAO	X. ±0.10 X.* ±2* .XX ±0.05 .XX* ±1*
These drawings and specifications are Shenzhen Yiyuan Technology Co Ltd. The property should not be copied. Without Shenzhen Yiyuan Technology Co. Ltd. Prior written consent to copy or use in any way.				