


[illegible]

REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	WPY 11/14/24'		



备注:

1. 电性说明:

1.1 耐压：500伏交流电一分钟

1.2 绝缘阻抗: 500兆欧最小

1.3 额定电流：2安

2. 环境特性:

2.1 工作温度: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$

3. 材料:

3.1 胶芯：PA66, 黑色

4. 产品符合欧盟RoHS环保要求

GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION		TITLE	
X.	±0.60	X.	±5°	UNITS	mm	2.0mm TJC8 TYPE 黑色1*18pin胶芯	
.X	±0.38	.X	±3°	SHEET SIZE	A4	SERIES	DS1071-01 SERIES
.XX	±0.25	.XX	±2°	 晨翔电子有限公司 CONNFLY CONNFLY ELECTRONIC CO. LTD			
DRAWING TYPE		CUSTOMER					
SCALE	1:1	SHEET	1 OF 1				
DRAWING NO.	C-DS1071-01-XXXXX-A						