








Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)




SPECIFICATIONS
Rated Current:3.0AMP
Contact Resistance:20mΩ Max
Withstand Voltage:1000V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:-40°C to +105°C

Contact Material:Brass
Contact Plating:Au or Sn Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PA6T
Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 10 seconds)



P = With Post



默认= W/O Post

Ordering Information

PM	254	-	*	-	N	-	S	-	*	-	**	-	*	-	P
No. of Rows 1=Single Row 2=Dual Row		No. of Pins 2~40Pin		Type 2-直插 8-弯插 S-立贴 R-带脚	Length (mm)		Contact G0:Gold Flash G1:1u" Gold G2:3u" Gold G3:5u" Gold G4:10u" Gold G5:15u" Gold G6:30u" Gold S0:Gold Flash/Tin S1:Tin	Plating	Packing R=Reel +Cap (编带+盖)		Post (带柱)				

			GENERAL TOLERANCE		制 图	 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	DRAWING				
			X. X	±0.30	审 核	产品名称		2.54双排 排母 贴片 编带+盖	版本
			X. XX	±0.20	批 准	TITLE		(塑高5.0)	REV.
			X. XXX	±0.10	APPROVAL	产品料号		PM254-2-N-S-5.0-XX-R(L5.3)	单 位
			Angle	±3.0°	SCALE	PART NO.			UNITS
					投影	材料			页 次
					Projection	MATERIAL			SHEET
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE							1/1