



W=With Bump



N=Without Bump

SPECIFICATIONS
Rated Current:3.0AMP
Contact Resistance:20mΩMax
Withstand Voltage:1000V AC/DC
Insulation Resistance:1000MΩMin
Operation Temperature:-40°C to +105°C

Contact Material:Brass
Contact Plating:Au Over Su
Insulator Material:Polyester(UL94V-0)
Standard: PBT

Note:
6P Without Slot "M" and "N"
8P~12P With Slot "M",Without Slot "N"
14P~64P With Slot "M" and "N"

Pin	Dimensions mm			
	A	B	C	D
6	12.42	5.08	6.35	12.12
8	14.96	7.62	8.89	14.66
10	17.50	10.16	11.43	17.20
12	20.04	12.70	13.97	19.74
14	22.58	15.24	16.51	22.28
16	25.12	17.78	19.05	24.82
18	27.66	20.32	21.59	27.36
20	30.20	22.86	24.13	29.90
24	35.28	27.94	29.21	34.98
26	37.82	30.48	31.75	37.52
28	40.36	33.02	34.29	40.06
30	42.90	35.56	36.83	42.60
32	45.44	38.10	39.37	45.14
34	47.98	40.64	41.91	47.68
40	55.60	48.26	49.53	55.30
44	60.68	53.34	54.61	60.38
50	68.30	60.96	62.23	68.00
60	81.00	73.66	74.93	80.70
64	86.08	78.74	80.01	85.78

Ordering Information

HC-NY 254 - * - N - * - * - * - * - * - *

No. of Rows 2=Dual Row
No. of Pins 6-64Pin
Type 1C=单接触 2C=双接触
Class Type 01=Straight Clasp 02=Butterfly Clasp
Contact Plating G0=Gold G1=10 Gold G2=Gold
Color B=Black G=Grey
Compose 2-2件 3-3件
Option Type BP=With Bump

			GENERAL TOLERANCE		制 图	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	DRAWING				
			X. X	±0.30	审 核	产品名称	2.54 双接触 反压扣(3件套)	版本	A
			X. XX	±0.20	批 准	TITLE		REV.	
			X. XXX	±0.10	APPROVAL	产品料号	HC-NY254-2-N-2C-01-XX-X-3-X	单位	mm
			Angle	±3.0°	SCALE	PART NO.		UNITS	
序号	变更内容	日期	投影		材料	页次	1/1		
No.	MODIFY CONTENT	MODIFY DATE	Projection		MATERIAL	SHEET			