

Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)

SPECIFICATIONS

Rated Current:1.5AMP
Contact Resistance:20mΩ Max
Withstand Voltage:500V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:-40°c to +105°c

Contact Material:Brass
Contact Plating:Au or Sn Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PA6T
Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 5 seconds)

Dimension antitheses list			
ITEM	PA	PB	W
Standard	4.00	2.50	6.50
Alternate			

Ordering Information

PZ 200 - * - N - S - C* - ** - DP

No. of Rows
1=Single Row
2=Dual Row


No. of Pins
2-40Pin

Type
S=直插
S=贴片
S=贴片

(双塑间距)

Contact Plating
G0:Gold Flash
G1:1u" Gold
G2:3u" Gold
G3:5u" Gold
G4:10u" Gold
G5:15u" Gold
G6:30u" Gold
S0:Gold Flash/Tin
S1:Tin

Double Plastic
(双塑)



N= W/O Post

W= With Post

			GENERAL TOLERANCE		制 图	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	DRAWING				
			X. X	±0.30	审 核	产品名称	2.00双排 双塑 排针 贴片	版本	A
			X. XX	±0.20	批 准	TITLE		REV.	
			X. XXX	±0.10	APPROVAL	产品料号	PZ200-2-N-S-C4.0-XX-DP	单 位	mm
			Angle	±3.0°	SCALE	PART NO.		UNITS	
序号	变更内容	日期	投影		投 影	材料		页 次	1/1
No.	MODIFY CONTENT	MODIFY DATE	Projection		Projection	MATERIAL		SHEET	