








SPECIFICATIONS
Rated Current:1.5AMP
Contact Resistance:20mΩ Max
Withstand Voltage:500V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:-40°c to +105°c

Contact Material:Brass
Contact Plating:Au or Sn Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PA6T
Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 10 seconds)

Pitch	H (mm)
2.00mm	1.0
	1.5
	2.0
	2.5
	3.0
	4.0

Dimension antitheses list				
ITEM	PA	PB	W	L
Standard	2.0	2.50	4.50	4.5

Ordering Information				
PZ 200 - * - N - * - * - ** - R - *				
No. of Rows 1=Single Row 2=Dual Row 3=Triple Row 4=Quadruple Row	No. of Pins 02-40Pin	Type □: 02Pin □: 04Pin □: 06Pin □: 08Pin	Length (mm)	Contact Plating G0:Gold Flash G1:1u" Gold G2:3u" Gold G3:5u" Gold G4:10u" Gold G5:15u" Gold G6:30u" Gold
R=Reel +Cap		1=TYPE 1 2=TYPE 2 (编带+盖)		

			GENERAL TOLERANCE	制图 DRAWING	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
			DIM TOL	审核 CHECK				
			X. X ±0.30	批准 APPROVAL	产品名称 TITLE	2.00 单排 排针 贴片 塑高2.0 编带+盖	版本 REV.	A
			X. XX ±0.20	比例 SCALE	产品料号 PART NO.	PZ200-1-N-S-2.0-XX-R-X(L4.5)	单位 UNITS	mm
			X. XXX ±0.10	投影 Projection	材料 MATERIAL		页次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°					