



2 Pin




3 Pin




SPECIFICATIONS


- 1、Current Rating: 13A AC, DC
- 2、Voltage Rating: 300V AC, DC
- 3、Temperatuer Range: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
- 4、Contact Resistance: $20\text{m}\Omega$ Max
- 5、Insulation Resistance: $1000\text{m}\Omega$ Min
- 6、Withstanding Voltang: 1500V AC/minute
- 7、Material: Housing Nylon66 UL94-V0(2)



4 Pin



5 Pin



Circuit	Part NO.	Dimensions mm				
		A	B	C	D	E
2	HC-63001-2EY-05	14.35	8.64	2.41	13.46	6.35
3	HC-63001-3EY-05	20.70				
4	HC-63001-4EY-05	27.05				
5	HC-63001-5EY-05	33.40				

Ordering Information

HC-63001 - N*** - * - 05

Pin
Type
Colour
默认-透明
N-红色
Y-蓝色
B-黑色
P-黄色
Y-绿色
M-白色
R-棕色

			GENERL TOLERANCE		制 图 DRAWING	 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	审 核 CHECK				
			X. X	± 0.30	批 准 APPROVAL	产品名称 TITLE	63001 (6.30) 单排 母孔座	版 本 REV.	A
1	初版发行		X. XX	± 0.20	比 例 SCALE	产品料号 PART NO.	HC-63001-NEY-05	单 位 UNITS	mm
			X. XXX	± 0.10					
序号 No.	变更内容 MODIFY CONTENT	日 期 MODIFY DATE	Angle	± 3.0°	投 影 Projection		材 料 MATERIAL	页 次 SHEET	1/1