



3x2 Pin




3x3 Pin




SPECIFICATIONS


1. Current Rating: 13A AC, DC
2. Voltage Rating: 300V AC, DC
3. Temperature Range: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
4. Contact Resistance: $20\text{m}\Omega$ Max
5. Insulation Resistance: $1000\text{m}\Omega$ Min
6. Withstanding Voltage: 1500V AC/minute
7. Material: Housing Nylon66 UL94-V0(2)



3x4 Pin



3x5 Pin



Circuit	Part NO.	Dimensions mm				
		A	B	C	D	E
2	HC-63001-3x2EY-05	14.35	12.90	6.99	26.13	6.35
3	HC-63001-3x3EY-05	20.70				
4	HC-63001-3x4EY-05	27.05				
5	HC-63001-3x5EY-05	33.40				

Ordering Information

HC-63001 - N*** - * - 05

Pin

Type

Colour

Y-孔座

默认-透明

W-母孔座

R-红色

L-蓝色

B-黑色

P-黄色

Y-绿色

M-白色

B-棕色

			GENERAL TOLERANCE		制图 DRAWING	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
			DIM	TOL	审核 CHECK				
			X.X	± 0.30	批准 APPROVAL	产品名称 TITLE	63001 (6.30) 三排 母孔座	版本 REV.	A
			X.XX	± 0.20	比例 SCALE	产品料号 PART NO.	HC-63001-3xNEY-05	单位 UNITS	mm
			X.XXX	± 0.10	投影 Projection	材料 MATERIAL		页次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle	$\pm 3.0^{\circ}$					